

WT28347 Cut Sheet

Wiha SlimLine #2 square insulated blade, 1000V insulation rating, 3.0in (76mm) shaft length, reduced shank.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WT28347>

Technical Specifications

| | |
|--------------------------|--------------|
| Brand | Wiha |
| Series | SlimLine |
| Item | Blade |
| Screwdriver Type | Insulated |
| Tip Type | Square |
| Tip Size | #2 |
| Insulated | Yes |
| Insulation Rating | 1000V |
| Overall Length | 3.0in (76mm) |

| | |
|-----------------------------|--|
| Shaft Length | 3.0in (76mm) |
| Shaft Diameter | 0.24in (6.1mm) |
| Reduced Shank | Yes |
| Finish | Black oxide |
| For Use With | SlimLine series handles |
| Application | Screwdriving |
| Applicable Standards | ASTM F-1505-0, CSA, EN/IEC 60900 and VDE 0682/part 201 |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |