

WT30747 Cut Sheet



Wiha SlimLine #2 PlusMinus insulated screwdriver, 1000V insulation rating, 3.9in (100mm) shaft length, reduced shank, SoftFinish cushion grip handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WT30747>

Technical Specifications

| | |
|--------------------------|---------------|
| Brand | Wiha |
| Series | SlimLine |
| Item | Screwdriver |
| Screwdriver Type | Insulated |
| Tip Type | PlusMinus |
| Tip Size | #2 |
| Insulated | Yes |
| Insulation Rating | 1000V |
| Overall Length | 8.6in (218mm) |

| | |
|-----------------------------|--|
| Shaft Length | 3.9in (100mm) |
| Shaft Diameter | 0.24in (6.1mm) |
| Reduced Shank | Yes |
| Handle Length | 4.7in (119mm) |
| Handle Type | SoftFinish cushion grip handle |
| Application | Screwdriving |
| Applicable Standards | ASTM F-1505-0, CSA, EN/IEC 60900 and VDE 0682/part 201 |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |