

# WT32005 Cut Sheet



Wiha SoftFinish 2.0mm slotted insulated screwdriver, 1000V insulation rating, 2.4in (60mm) shaft length, SoftFinish cushion grip handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WT32005>

## Technical Specifications

|                          |             |                             |  |
|--------------------------|-------------|-----------------------------|--|
| <b>Brand</b>             | Wiha        | <b>Overall Length</b>       | 6.5in (165mm)  |
| <b>Series</b>            | SoftFinish  | <b>Shaft Length</b>         | 2.4in (60mm)   |
| <b>Item</b>              | Screwdriver | <b>Shaft Diameter</b>       | 0.20in (5.1mm)   |
| <b>Screwdriver Type</b>  | Insulated   | <b>Handle Length</b>        | 4.1in (104mm)  |
| <b>Tip Type</b>          | Slotted     | <b>Handle Type</b>          | SoftFinish cushion grip handle                         |
| <b>Tip Size</b>          | 2.0mm       | <b>Application</b>          | Screwdriving   |
| <b>Insulated</b>         | Yes         | <b>Applicable Standards</b> | ASTM F-1505-0, CSA, EN/IEC 60900 and VDE 0682/part 201 |
| <b>Insulation Rating</b> | 1000V       |                             |  |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | None                                   |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | None                                   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | No                                     |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |