

WT32023 Cut Sheet



Wiha 4.5mm slotted insulated screwdriver, 1000V insulation rating, 3.9in (100mm) shaft length, SoftFinish cushion grip handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WT32023>

Technical Specifications

| | | | |
|------------------------------|---------------|-----------------------------|--|
| Brand | Wiha | Shaft Length | 3.9in (100mm) |
| Item | Screwdriver | Shaft Diameter | 0.24in (6.1mm) |
| Screwdriver Type | Insulated | Reduced Shank | No |
| Tip Type | Slotted | Finish | Black oxide |
| Tip Size | 4.5mm | Handle Length | 4.4in (112mm) |
| Slotted Tip Thickness | 1.0mm | Handle Type | SoftFinish cushion grip handle |
| Insulated | Yes | Application | Screwdriving |
| Insulation Rating | 1000V | Applicable Standards | ASTM F-1505-0, CSA, EN/IEC 60900 and VDE 0682/part 201 |
| Overall Length | 8.3in (211mm) | | |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |