

WT32024 Cut Sheet



Wiha SoftFinish 4.5mm slotted insulated screwdriver, 1000V insulation rating, 4.9in (125mm) shaft length, SoftFinish cushion grip handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WT32024>

Technical Specifications

Brand	Wiha	Overall Length	9.3in (236mm)
Series	SoftFinish	Shaft Length	4.9in (125mm)
Item	Screwdriver	Shaft Diameter	0.32in (8.1mm)
Screwdriver Type	Insulated	Handle Type	SoftFinish cushion grip handle
Tip Type	Slotted	Application	Screwdriving
Tip Size	4.5mm	Applicable Standards	ASTM F-1505-0, CSA, EN/IEC 60900 and VDE 0682/part 201
Insulated	Yes		
Insulation Rating	1000V		

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document