

# WT32103 Cut Sheet

Wiha SoftFinish #3 Phillips insulated screwdriver, 1000V insulation rating, 6.0in (150mm) shaft length, SoftFinish cushion grip handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WT32103>



## Technical Specifications

Brand	Wiha	Overall Length	10.6in (269mm)
Series	SoftFinish	Shaft Length	6.0in (150mm)
Item	Screwdriver	Shaft Diameter	0.45in (11.4mm)
Screwdriver Type	Insulated	Handle Length	4.7in (119mm)
Tip Type	Phillips	Handle Type	SoftFinish cushion grip handle
Tip Size	#3	Application	Screwdriving
Insulated	Yes	Applicable Standards	ASTM F-1505-0, CSA, EN/IEC 60900 and VDE 0682/part 201
Insulation Rating	1000V		

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>