

WT32490 Cut Sheet



Wiha SlimLine SpeedE II insulated multi-bit electric screwdriver, 1000V insulation rating, 13 pieces, SoftFinish cushion grip handle, 2.1in (53mm) shaft length, slotted, Phillips, square and PlusMinus.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WT32490>

Technical Specifications

Brand	Wiha
Series	SlimLine SpeedE II
Item	Screwdriver
Screwdriver Type	Insulated multi-bit electric
Number of Pieces	13
Ratcheting	No
Insulated	Yes
Insulation Rating	1000V
Overall Length	10.2in (259mm)
Shaft Length	2.1in (53mm)
Shaft Diameter	0.24in (6.1mm)

Handle Length	5.4in (137mm)
Handle Type	SoftFinish cushion grip handle
Tip Type	Slotted, Phillips, square and PlusMinus
Includes	(1) SpeedE II electric handle, (8) SlimLine blades (slotted (3.5mm, 5.5mm), Phillips (#1, #2), square (#1, #2), PlusMinus (#1, #2), (1) adapter plug, (1) battery charger, (2) replaceable lithium-ion batteries, (1) L-Box Mini storage box
Application	Screwdriving
Applicable Standards	ASTM F-1505-0, CSA, EN/IEC 60900 and VDE 0682/part 201

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document