

# WT32636 Cut Sheet



Wiha diagonal cutters, 8.0in (203mm) overall length, induction hardened beveled cutting edges, 15 degrees angled head, classic grip vinyl handles. Power button for increasing cutting capacity.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WT32636>

## Technical Specifications

<b>Brand</b>	Wiha
<b>Item</b>	Cutters
<b>Pliers Type</b>	Diagonal
<b>Overall Length</b>	8.0in (203mm)
<b>Insulated</b>	No
<b>Cutting</b>	Induction hardened beveled cutting edges
<b>Angled Head</b>	15 degrees
<b>Handle Type</b>	Classic grip vinyl handles
<b>Application</b>	Wire cutting and chain cutting
<b>Material</b>	C70 steel
<b>Additional Information</b>	Power button for increasing cutting capacity

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>