

WT32926 Cut Sheet



Wiha long nose pliers, 6.3in (160mm) overall length, insulated, 1000V insulation rating, induction hardened beveled cutting edges, insulated cushion grip handles.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WT32926>

Technical Specifications

Brand	Wiha
Item	Pliers
Pliers Type	Long nose
Overall Length	6.3in (160mm)
Insulated	Yes
Insulation Rating	1000V
Cutting	Induction hardened beveled cutting edges
Capacity	10 AWG
Handle Type	Insulated cushion grip handles
Application	Gripping and wire cutting
Material	C70 steel
Applicable Standards	ASTM F-1505-0, CSA, EN/IEC 60900 and VDE 0682/part 201

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document