

# WT32928 Cut Sheet



Wiha bent nose pliers, 6.3in (160mm) overall length, insulated, 1000V insulation rating, induction hardened beveled cutting edges, insulated cushion grip handles.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WT32928>

## Technical Specifications

<b>Brand</b>	Wiha
<b>Item</b>	Pliers
<b>Pliers Type</b>	Bent nose
<b>Overall Length</b>	6.3in (160mm)
<b>Insulated</b>	Yes
<b>Insulation Rating</b>	1000V
<b>Cutting</b>	Induction hardened beveled cutting edges
<b>Handle Type</b>	Insulated cushion grip handles
<b>Application</b>	Gripping and wire cutting
<b>Material</b>	C70 steel
<b>Applicable Standards</b>	ASTM F-1505-0, CSA, EN/IEC 60900 and VDE 0682/part 201

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>