

# WT35812 Cut Sheet



Wiha #2 square insulated screwdriver, 1000V insulation rating, 5.9in (150mm) shaft length, SoftFinish cushion grip handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WT35812>

## Technical Specifications

<b>Brand</b>	Wiha
<b>Item</b>	Screwdriver
<b>Screwdriver Type</b>	Insulated
<b>Tip Type</b>	Square
<b>Tip Size</b>	#2
<b>Insulated</b>	Yes
<b>Insulation Rating</b>	1000V
<b>Overall Length</b>	10.6in (269mm)

<b>Shaft Length</b>	5.9in (150mm)
<b>Shaft Diameter</b>	0.25in (6.4mm)
<b>Reduced Shank</b>	No
<b>Handle Length</b>	4.7in (119mm)
<b>Handle Type</b>	SoftFinish cushion grip handle
<b>Application</b>	Screwdriving
<b>Applicable Standards</b>	ASTM F-1505-0, CSA, EN/IEC 60900 and VDE 0682/part 201

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>