

WT41101 Cut Sheet



Wiha Digi-Max series digital caliper, 0–6in (152mm) range, 0.0005in and 0.01mm accuracy.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WT41101>

Technical Specifications

| | |
|----------------------|---------------------|
| Brand | Wiha |
| Item | Caliper |
| Series | Digi-Max |
| Display Type | Digital |
| Measuring Range (PF) | 0–6in (152mm) |
| Accuracy | 0.0005in and 0.01mm |
| Measurement Type | Imperial and metric |
| Jaw Material | Steel |
| Jaw Depth | 1.6in |

| | |
|------------------------|--|
| Caliper Measurements | Depth, inside, outside and step |
| Caliper Material | Non metallic, non magnetic plastic |
| Includes | SR44 battery and printed instruction insert |
| Application | Measurement |
| Additional Information | Bi-directional thumb roller with friction stop, pushbutton for inch to metric conversion, switches on automatically when opened, switches off after 5 minutes of non-use |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |