

WT61630 Cut Sheet



Wiha folding ruler, insulated, 1000V insulation rating, 6.5ft/2m length, metric inside and imperial outside reading, 1/16in and 1mm marks, 10 sections, 0, 90, and 180 degree lock-in-place stop-joints.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WT61630>

Technical Specifications

Brand	Wiha	Insulated	Yes
Item	Folding ruler	Insulation Rating	1000V
Measurement Reading	Metric inside and imperial outside	Material	30% fiberglass composite
Length	6.5ft/2m	Lock Type	0, 90, and 180 degree lock-in-place stop-joints
Closed Length	9in	Color	Red
Number of Sections	10	Application	Measurement
Graduation Marks	1/16in and 1mm	Additional Information	Integrated wire pulling slot for pulling wire gauged between 3–7mm, notched markings, 40% more rigid when extended
Width	5/8in		
Thickness	1/8in		

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document