

# WT77890 Cut Sheet

Wiha SoftFinish multi-bit reversible shaft screwdriver, 4 pieces, SoftFinish cushion grip handle, 3.0in (75mm) shaft length, slotted and Phillips.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WT77890>



## Technical Specifications

Brand	Wiha
Series	SoftFinish
Item	Screwdriver
Screwdriver Type	Multi-bit reversible shaft
Number of Pieces	4
Ratcheting	No
Insulated	No
Lock Mechanism	Ballpoint bit
Overall Length	8.3in (211mm)
Shaft Length	3.0in (75mm)

Shaft Diameter	0.43in (10.9mm)
Handle Length	5.3in (135mm)
Handle Type	SoftFinish cushion grip handle
Tip Type	Slotted and Phillips
Includes	(1) SoftFinish cushion grip handle, (1) reversible shaft with 2 nutdriver profiles (1/4in, 5/16in), (1) Phillips double-ended bit (#1, #2), (1) slotted double-ended bit (3/16in, 1/4in)
Application	Screwdriving and nut driving

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>