

WT77891 Cut Sheet

Wiha SoftFinish multi-bit reversible shaft screwdriver, 8 pieces, SoftFinish cushion grip handle, 3.0in (75mm) shaft length, slotted, Phillips, square and Torx.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WT77891>



Technical Specifications

Brand	Wiha	Shaft Diameter	0.53in (13.5mm)
Series	SoftFinish	Handle Length	5.3in (135mm)
Item	Screwdriver	Handle Type	SoftFinish cushion grip handle
Screwdriver Type	Multi-bit reversible shaft	Tip Type	Slotted, Phillips, square and Torx
Number of Pieces	8	Includes	(1) SoftFinish cushion grip handle, (1) reversible shaft with 2 nutdriver profiles (5/16in, 3/8in), (2) double-ended bit holders w/ 1/4in nutdriving capacity, (4) double-ended bits (Phillips: #1, #2, slotted: 3/16in, 1/4in, Torx: T20, T25, square: #1, #2)
Ratcheting	No		
Insulated	No	Application	Screwdriving and nut driving
Lock Mechanism	Ballpoint bit		
Overall Length	8.3in (211mm)		
Shaft Length	3.0in (75mm)		

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document