

# WT77892 Cut Sheet



Wiha SoftFinish multi-bit reversible shaft screwdriver, 5 pieces, SoftFinish cushion grip handle, 2.4in (60mm) shaft length, slotted and Phillips.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WT77892>

## Technical Specifications

<b>Brand</b>	Wiha
<b>Series</b>	SoftFinish
<b>Item</b>	Screwdriver
<b>Screwdriver Type</b>	Multi-bit reversible shaft
<b>Number of Pieces</b>	5
<b>Ratcheting</b>	No
<b>Insulated</b>	No
<b>Lock Mechanism</b>	Ballpoint bit
<b>Overall Length</b>	8.3in (211mm)
<b>Shaft Length</b>	2.4in (60mm)

<b>Handle Length</b>	5.4in (137mm)
<b>Handle Type</b>	SoftFinish cushion grip handle
<b>Tip Type</b>	Slotted and Phillips
<b>Includes</b>	(1) SoftFinish cushion grip handle, (1) interchangeable conduit reamer (1/2in, 3/4in, 1in), (1) reversible shaft with 2 nutdriver profiles (1/4in, 5/16in), (1) Phillips double-ended bit (#1, #2), (1) slotted double-ended bit (3/16in, 1/4in)
<b>Application</b>	Screwdriving, conduit reaming and nut driving

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>