

WT91872 Cut Sheet



Wiha electricians set, 59 pieces, imperial, tool backpack.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WT91872>

Technical Specifications

Brand	Wiha
Item	Electrician's set
Number of Pieces	59
Measurement Type	Imperial
Set Includes	<ul style="list-style-type: none">• (1) category IV voltage detector 110V• (1) insulated V-Jaw tongue and groove pliers 10in• (1) 13 piece imperial ErgoStar ball-end hex L-key set• (1) 9 piece metric ErgoStar ball-end hex L-key set• (3) 4in magnetic nut setter 1/4in drive (1/4in, 3/8in, 1/2in)• (10) insulated SlimLine SoftFinish screwdrivers (Phillips/slotted (#1, #2), slotted (4mm, 4.5mm, 5.5mm, 6.5mm), Phillips (#1, #2), square (#1, #2))• (6) insulated SoftFinish nutdriver (7/32in, 1/4in, 5/16in, 3/8in, 7/16in, 1/2in)• (1) classic auto grip V-Jaw tongue and groove pliers 10in• (1) insulated long nose pliers 8in• (1) insulated cable cutters 8in• (1) insulated lineman's pliers 9.5in• (1) insulated high leverage angle cutters 8in• (1) SoftFinish heavy duty slotted screwdriver (10mm)• (1) classic grip wire strippers 7.25in• (1) 25ft DualMax tape measure• (1) claw hammer 20 oz• (6) insulated PicoFinish precision screwdriver (slotted (2.5mm, 3mm, 3.5mm), Phillips (#00, #0, #1)• (1) heavy duty tool hauler backpack
Package Type	Tool backpack

Set Includes	<ul style="list-style-type: none">• (1) category IV voltage detector 110V• (1) insulated V-Jaw tongue and groove pliers 10in• (1) 13 piece imperial ErgoStar ball-end hex L-key set• (1) 9 piece metric ErgoStar ball-end hex L-key set• (3) 4in magnetic nut setter 1/4in drive (1/4in, 3/8in, 1/2in)• (10) insulated SlimLine SoftFinish screwdrivers (Phillips/slotted (#1, #2), slotted (4mm, 4.5mm, 5.5mm, 6.5mm), Phillips (#1, #2), square (#1, #2))• (6) insulated SoftFinish nutdriver (7/32in, 1/4in, 5/16in, 3/8in, 7/16in, 1/2in)• (1) classic auto grip V-Jaw tongue and groove pliers 10in• (1) insulated long nose pliers 8in• (1) insulated cable cutters 8in• (1) insulated lineman's pliers 9.5in• (1) insulated high leverage angle cutters 8in• (1) SoftFinish heavy duty slotted screwdriver (10mm)• (1) classic grip wire strippers 7.25in• (1) 25ft DualMax tape measure• (1) claw hammer 20 oz• (6) insulated PicoFinish precision screwdriver (slotted (2.5mm, 3mm, 3.5mm), Phillips (#00, #0, #1)• (1) heavy duty tool hauler backpack
Package Type	Tool backpack

WT91872 Cut Sheet

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document