

WT92100 Cut Sheet



Wiha contractor set, 194 pieces.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WT92100>

Technical Specifications

Brand	Wiha
Item	Contractor set
Number of Pieces	194

Set Includes

- (7) SoftFinish standard screwdrivers (slotted (4.5mm, 6.5mm, 8.0mm), Phillips (#1, #2)
- (2) SoftFinish heavy duty screwdrivers (slotted 8.0mm, Phillips #2)
- (1) SoftFinish 11inOne multi-bit screwdriver
- (1) SoftFinish CentroFix blade holder
- (1) 9in magnetic torpedo level
- (1) 25ft DualMax tape measure
- (1) 20oz claw hammer
- (1) Non-contact voltage tester (Category IV 12-1000VAC) with flash light
- (1) 36pc GoBox electronics ESD precision micro bit set
- (1) 32pc GoBox TerminatorBlue impact bit set with mini ratchet
- (1) 6pc color coded magnetic nut setter imperial set
- (1) 6 Piece color coded magnetic nut setter metric set
- (1) 10in classic auto grip V-jaw tongue and groove pliers
- (1) 10.25in classic grip pliers wrench
- (1) 8in classic grip high leverage combination pliers
- (1) 8in classic grip BiCut compound diagonal cutters
- (1) 8.25in classic grip wire combination strippers/ crimpers
- (1) classic grip flush cutters with return spring
- (1) 8in classic grip long nose pliers w/ cutters
- (1) 9.5in classic grip NE style lineman's pliers with crimpers
- (1) 22pc ErgoStar ball end hex L-key set - inch/ metric
- (1) 13pc torx rust free finish L-key set
- (12) combination wrenches - inch/metric (8-15mm, 5/16-5/8in)
- (21) 12 point - 3/8in drive sockets - inch/metric (1/4-7/8in, 6-22mm)
- (20) 12 point - 3/8in drive deep socket - inch/ metric(1/4-7/8in, 8-22mm)
- (1) Lockable watertight case with trolley and wheels for easy transportation

WT92100 Cut Sheet

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document