

XBE-DC32A Cut Sheet



LS Electric XGB discrete input module, 32-point, 24 VDC, sinking/sourcing, 1 common(s), 32 point(s) per common. Requires XTB-40H terminal block and C40HH-xxSB-XBI cable.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/XBE-DC32A>

Technical Specifications

Brand	LS Electric XGB
Item	Input module
I/O Module Type	Discrete
Number of Input Points	32
Nominal Input Voltage	24 VDC
Discrete Input Type	Sinking/sourcing
Fast Response	No
Number of Non-Isolated Input Commons	1
Number of Points per Common	32
External Power Requirement	24 VDC
Requires	XTB-40H terminal block and C40HH-xxSB-XBI cable
Programming Software	XG5000 programming software v4.7 or later

Agency Approvals

UL Listed File #	E124950
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document