

# XBE-DR16A Cut Sheet



LS Electric XGB discrete combo module, Input: 8-point, 24 VDC, sinking/sourcing, Output: 8-point, 125 VDC/250 VAC, relay, (8) Form A (SPST) relays, 2A/point, 5A/common. Removable terminal blocks included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/XBE-DR16A>

## Technical Specifications

<b>Brand</b>	LS Electric XGB
<b>Item</b>	Combo module
<b>I/O Module Type</b>	Discrete
<b>Number of Input Points</b>	8
<b>Nominal Input Voltage</b>	24 VDC
<b>Discrete Input Type</b>	Sinking/sourcing
<b>Number of Non-Isolated Discrete Input Commons</b>	1
<b>Number of Points per Discrete Input Common</b>	8
<b>Number of Output Points</b>	8

<b>Nominal Output Voltage</b>	125 VDC/250 VAC
<b>Discrete Output Type</b>	Relay
<b>Relay Configuration</b>	(8) Form A (SPST) relays
<b>Number of Non-Isolated Discrete Output Commons</b>	1
<b>Number of Points per Discrete Output Common</b>	8
<b>Load Current</b>	2A/point, 5A/common
<b>Fuse Type</b>	User-supplied external fuse
<b>Includes</b>	Removable terminal blocks
<b>Programming Software</b>	XG5000 programming software v4.7 or later

## Agency Approvals

<b>UL Listed File #</b>	E124950
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	View CE declarations
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	View EU REACH document

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/XBE-DR16A.pdf>  
See store item page for other formats.