

XBE-RY08A Cut Sheet



LS Electric XGB relay output module, 8-point, 125 VDC/250 VAC, (8) Form A, 1 common(s), 8 point(s) per common, 2A/point, 5A/common. Removable terminal block included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/XBE-RY08A>

Technical Specifications

Brand	LS Electric XGB
Item	Output module
I/O Module Type	Relay
Number of Output Points	8
Nominal Output Voltage	125 VDC/250 VAC
Relay Configuration	(8) Form A (SPST) relays
Number Of Commons	1
Jumper Selectable Isolation	No

Number of Points per Common	8
Load Current	2A/point, 5A/common
Fuse Type	User-supplied external fuse
Includes	Removable terminal block
Programming Software	XG5000 programming software v4.7 or later

Agency Approvals

UL Listed File #	E124950
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/XBE-RY08A.pdf>
See store item page for other formats.