

# XBE-TN08A Cut Sheet



LS Electric XGB discrete output module, 8-point, 12-24 VDC, sinking, 1 common(s), 8 point(s) per common, 0.5A/point, 2A/common. Removable terminal blocks included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/XBE-TN08A>

## Technical Specifications

<b>Brand</b>	LS Electric XGB
<b>Item</b>	Output module
<b>I/O Module Type</b>	Discrete
<b>Number of Output Points</b>	8
<b>Nominal Output Voltage</b>	12-24 VDC
<b>Discrete Output Type</b>	Sinking
<b>Number of Non-Isolated Output Commons</b>	1

<b>Number of Points per Common</b>	8
<b>Load Current</b>	0.5A/point, 2A/common
<b>External Power Requirement</b>	12-24 VDC
<b>Includes</b>	Removable terminal blocks
<b>Programming Software</b>	XG5000 programming software v4.7 or later

## Agency Approvals

<b>UL Listed File #</b>	E124950
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/XBE-TN08A.pdf>  
See store item page for other formats.