

XBE-TP16A Cut Sheet



LS Electric XGB discrete output module, 16-point, 12-24 VDC, sourcing, 1 common(s), 16 point(s) per common, 0.5A/point, 2A/common. Removable terminal blocks included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/XBE-TP16A>

Technical Specifications

Brand	LS Electric XGB
Item	Output module
I/O Module Type	Discrete
Number of Output Points	16
Nominal Output Voltage	12-24 VDC
Discrete Output Type	Sourcing
Number of Non-Isolated Output Commons	1

Number of Points per Common	16
Load Current	0.5A/point, 2A/common
External Power Requirement	24 VDC
Includes	Removable terminal blocks
Programming Software	XG5000 programming software v4.7 or later

Agency Approvals

UL Listed File #	E124950
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/XBE-TP16A.pdf>
See store item page for other formats.