

XBE-TP32A Cut Sheet



LS Electric XGB discrete output module, 32-point, 12-24 VDC, sourcing, 1 common(s), 32 point(s) per common, 0.2A/point, 2A/common. Requires XTB-40H terminal block and C40HH-xxSB-XBI cable.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/XBE-TP32A>

Technical Specifications

Brand	LS Electric XGB
Item	Output module
I/O Module Type	Discrete
Number of Output Points	32
Nominal Output Voltage	12-24 VDC
Discrete Output Type	Sourcing
Number of Non-Isolated Output Commons	1

Number of Points per Common	32
Load Current	0.2A/point, 2A/common
External Power Requirement	24 VDC
Requires	XTB-40H terminal block and C40HH-xxSB-XBI cable
Programming Software	XG5000 programming software v4.7 or later

Agency Approvals

UL Listed File #	E124950
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/XBE-TP32A.pdf>
See store item page for other formats.