

XBF-AH04A Cut Sheet



LS Electric XGB analog combo module, Input: 2-channel, current/voltage, 0-20 mA and 4-20 mA, 0-5 VDC, 1-5 VDC and 0-10 VDC, Output: 2-channel, current/voltage, 0-20 mA and 4-20 mA, 0-5 VDC, 1-5 VDC and 0-10 VDC.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/XBF-AH04A>

Technical Specifications

Brand	LS Electric XGB
Item	Combo module
I/O Module Type	Analog
Number of Input Channels	2
Input Signal Type(s)	Current/voltage
Number of Non-Isolated Input Commons	2
Input Resolution	12-bit
Input Current Signal Range	0-20 mA and 4-20 mA
Input Voltage Signal Range	0-5 VDC, 1-5 VDC and 0-10 VDC
Number of Output Channels	2
Output Signal Type	Current/voltage
Number of Non-Isolated Output Commons	2
Output Resolution	12-bit
Output Current Signal Range	0-20 mA and 4-20 mA
Output Voltage Signal Range	0-5 VDC, 1-5 VDC and 0-10 VDC
External Power Requirement	24 VDC
Includes	Removable terminal block
Programming Software	XG5000 programming software v4.7 or later

Agency Approvals

UL Listed File #	E124950
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document