

# XBF-DV04C Cut Sheet



LS Electric XGB analog output module, 4-channel, voltage, 14-bit, output voltage signal range(s) of 0-5 VDC, 1-5 VDC, 0-10 VDC and +/- 10 VDC, external 24 VDC required.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/XBF-DV04C>

## Technical Specifications

<b>Brand</b>	LS Electric XGB
<b>Item</b>	Output module
<b>I/O Module Type</b>	Analog
<b>Number Of Output Channels</b>	4
<b>Output Signal Type</b>	Voltage
<b>Isolated Channels</b>	No
<b>Number of Non-Isolated Output Commons</b>	4
<b>Output Resolution</b>	14-bit
<b>Output Voltage Signal Range</b>	0-5 VDC, 1-5 VDC, 0-10 VDC and +/- 10 VDC
<b>External Power Requirement</b>	24 VDC
<b>Includes</b>	Removable terminal block
<b>Programming Software</b>	XG5000 programming software v4.7 or later

## Agency Approvals

<b>UL Listed File #</b>	E124950
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>