

XBF-TC04S Cut Sheet



LS Electric XGB temperature input module, thermocouple, 4-channel, 16-bit resolution, input thermocouple type(s): J, K, R, T. Removable terminal block included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/XBF-TC04S>

Technical Specifications

Brand	LS Electric XGB
Item	Input module
I/O Module Type	Temperature
Input Signal Type(s)	Thermocouple
Number Of Input Channels	4
Input Thermocouple Signal Type	J, K, R, T
Input Resolution	16-bit
External Power Requirement	External 24 VDC required
Includes	Removable terminal block
Programming Software	XG5000 programming software v4.7 or later

Agency Approvals

UL Listed File #	E124950
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/XBF-TC04S.pdf>
See store item page for other formats.