

XCS-0K2L3F22A Cut Sheet



Killark control station cover assembly, hazardous location rated, single selector switch, key-operated, 2-position, black, spring return from right, (1) N.O./(1) N.C. contact(s), legend plate marking "OFF ON".

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/XCS-0K2L3F22A>

Technical Specifications

Brand	Killark
Item	Control station cover assembly
Application	Hazardous location rated
Factory Sealed	No
Housing Material	Aluminum
Control Station Configuration	Single selector switch
Number Of Positions	2
Key Removable Position	Key removable left position
Operator Type	Key-operated
Operator Color	Black
Action	Spring return from right
Contact Type	(1) N.O./(1) N.C.
Legend Plate Marking	OFF ON
NEMA Rating	7/9
Requires	SWB series deep style splice/device box

Agency Approvals

UL Listed File #	E53360
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	LR11714
RoHS Status	No
EU REACH	View EU REACH document