

# XCS-0K3R6G32A Cut Sheet



Killark control station cover assembly, hazardous location rated, single selector switch, key-operated, 3-position, black, spring return to center from left, maintained center and right, (2) N.O. contact(s), legend plate marking "HAND OFF AUTO".

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/XCS-0K3R6G32A>

## Technical Specifications

<b>Brand</b>	Killark
<b>Item</b>	Control station cover assembly
<b>Application</b>	Hazardous location rated
<b>Factory Sealed</b>	No
<b>Housing Material</b>	Aluminum
<b>Control Station Configuration</b>	Single selector switch
<b>Number Of Positions</b>	3
<b>Key Removable Position</b>	Key removable center position
<b>Operator Type</b>	Key-operated
<b>Operator Color</b>	Black
<b>Action</b>	Spring return to center from left, maintained center and right
<b>Contact Type</b>	(2) N.O.
<b>Legend Plate Marking</b>	HAND OFF AUTO
<b>NEMA Rating</b>	7/9
<b>Requires</b>	SWB series deep style splice/device box

## Agency Approvals

<b>UL Listed File #</b>	E53360
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	LR11714
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>