

XCS-0MMK3 Cut Sheet



Killark control station cover assembly, hazardous location rated, (1) pushbutton, mushroom, black, push-pull, (1) N.O./ (1) N.C. contact(s), (3) two-sided legend plate(s), legend plate marking "START,STOP / EMERGENCY STOP, RESET / blank, RESET".

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/XCS-0MMK3>

Technical Specifications

| | |
|--------------------------------------|--------------------------------|
| Brand | Killark |
| Item | Control station cover assembly |
| Application | Hazardous location rated |
| Factory Sealed | No |
| Housing Material | Aluminum |
| Control Station Configuration | (1) pushbutton |
| Operator Type | Mushroom |
| Operator Size | 40mm |

| | |
|-----------------------------|---|
| Operator Color | Black |
| Action | Push-pull |
| Contact Type | (1) N.O./ (1) N.C. |
| Legend Plate Type | (3) two-sided |
| Legend Plate Marking | START,STOP / EMERGENCY STOP, RESET / blank, RESET |
| NEMA Rating | 7/9 |
| Requires | SWB series splice/device box |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E53360 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | LR11714 |
| RoHS Status | No |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/XCS-0MMK3.pdf>
See store item page for other formats.