

XCS-0S3L6G Cut Sheet



Killark control station cover assembly, hazardous location rated, single selector switch, knob, 3-position, black, spring return to center from right, maintained center and left, (2) N.O. contact(s), legend plate marking "HAND OFF AUTO".

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/XCS-0S3L6G>

Technical Specifications

Brand	Killark	Operator Type	Knob
Item	Control station cover assembly	Operator Color	Black
Application	Hazardous location rated	Action	Spring return to center from right, maintained center and left
Factory Sealed	No	Contact Type	(2) N.O.
Housing Material	Aluminum	Legend Plate Marking	HAND OFF AUTO
Control Station Configuration	Single selector switch	NEMA Rating	7/9
Number Of Positions	3	Requires	SWB series deep style splice/device box

Agency Approvals

UL Listed File #	E53360
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	LR11714
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/XCS-0S3L6G.pdf>
See store item page for other formats.