

XCS-0S3R6G Cut Sheet



Killark control station cover assembly, hazardous location rated, single selector switch, knob, 3-position, black, spring return to center from left, maintained center and right, (2) N.O. contact(s), legend plate marking "HAND OFF AUTO".

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/XCS-0S3R6G>

Technical Specifications

Brand	Killark
Item	Control station cover assembly
Application	Hazardous location rated
Factory Sealed	No
Housing Material	Aluminum
Control Station Configuration	Single selector switch
Number Of Positions	3

Operator Type	Knob
Operator Color	Black
Action	Spring return to center from left, maintained center and right
Contact Type	(2) N.O.
Legend Plate Marking	HAND OFF AUTO
NEMA Rating	7/9
Requires	SWB series deep style splice/device box

Agency Approvals

UL Listed File #	E53360
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	LR11714
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/XCS-0S3R6G.pdf>
See store item page for other formats.