


XGC220390-091 Cut Sheet



Velox machine guarding door, left hinged, swing out, 36 x 96in, 2 x 2in grid, carbon steel, yellow and black. 2 door posts XG5508D and mounting hardware included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/XGC220390-091>

Technical Specifications

Brand	Velox
Door Type	Left hinged
Open Direction	Swing out
Door Size	36 x 96in
Overall Width	39.25in
Grid Size	2 x 2in
Wire Thickness	8 gauge
Material	Carbon steel

Finish	Powder coat
Color	Yellow and black
Number of Hinges Per Door	4
Hinge Type	Drop pin
Number Of Latches	1
Latch Type	Snap
Includes	2 door posts XG5508D and mounting hardware

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/XGC220390-091.pdf>
See store item page for other formats.