

# XTH-0100F-K Cut Sheet



ProSense temperature transmitter, isolated, Type K thermocouple input, 0 to 100 deg F fixed, 4-20 mA output, 8-35 VDC operating voltage, DIN Form B connection head mount, screw terminals.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/XTH-0100F-K>

## Technical Specifications

Brand	ProSense	Output Current	4-20 mA
Item	Temperature transmitter	Signal Range	
Isolation	Isolated	Operating Voltage	8-35 VDC
Field Configurable	No	Housing Material	Plastic
Input Thermocouple	Type K thermocouple	Mounting	DIN Form B connection head
Signal Type		Electrical Connection	Screw terminals
Factory Calibrated	0 to 100 deg F fixed	Includes	Mounting screws
Temperature Range			

## Agency Approvals

UL Listed File #	None
UL Recognized File #	E311366
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/XTH-0100F-K.pdf>  
See store item page for other formats.