

XTH-01500F-K Cut Sheet



ProSense temperature transmitter, isolated, Type K thermocouple input, 0 to 1500 deg F fixed, 4-20 mA output, 8 to 35 VDC operating voltage, DIN Form B connection head mount, screw terminals.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/XTH-01500F-K>

Technical Specifications

| | |
|---|----------------------------|
| Brand | ProSense |
| Item | Temperature transmitter |
| Isolation | Isolated |
| Field Configurable | No |
| Input Thermocouple Signal Type | Type K thermocouple |
| Factory Calibrated Temperature Range | 0 to 1500 deg F fixed |
| Output Current Signal Range | 4-20 mA |
| Operating Voltage | 8 to 35 VDC |
| Housing Material | Plastic |
| Mounting | DIN Form B connection head |
| Electrical Connection | Screw terminals |
| Includes | Mounting screws |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | E311366 |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |