

XTH-0200F-K Cut Sheet



ProSense temperature transmitter, isolated, Type K thermocouple input, 0 to 200 deg F fixed, 4-20 mA output, 8-35 VDC operating voltage, DIN Form B connection head mount, screw terminals.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/XTH-0200F-K>

Technical Specifications

Brand	ProSense
Item	Temperature transmitter
Isolation	Isolated
Field Configurable	No
Input Thermocouple Signal Type	Type K thermocouple
Factory Calibrated Temperature Range	0 to 200 deg F fixed

Output Current	4-20 mA
Signal Range	
Operating Voltage	8-35 VDC
Housing Material	Plastic
Mounting	DIN Form B connection head
Electrical Connection	Screw terminals
Includes	Mounting screws

Agency Approvals

UL Listed File #	None
UL Recognized File #	E311366
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/XTH-0200F-K.pdf>
See store item page for other formats.