

# XTH-0800F-K Cut Sheet



ProSense temperature transmitter, isolated, Input: 1-channel, Type K thermocouple, 0 to 800 deg F fixed, Output: 1-channel, output current signal range(s) of 4-20 mA, 8-35 VDC operating voltage, DIN Form B connection head mount, screw terminals.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/XTH-0800F-K>

## Technical Specifications

Brand	ProSense
Item	Temperature transmitter
Isolation	Isolated
Field Configurable	No
Number Of Input Channels	1
Input	Thermocouple
Input Thermocouple Signal Type	K
Factory Calibrated Temperature Range	0 to 800 deg F fixed

Number Of Output Channels	1
Output	Current
Output Current Signal Range	4-20 mA
Operating Voltage	8-35 VDC
Housing Material	Plastic
Mounting	DIN Form B connection head
Electrical Connection	Screw terminals
Includes	Mounting screws

## Agency Approvals

UL Listed File #	None
UL Recognized File #	E311366
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/XTH-0800F-K.pdf>  
See store item page for other formats.