

# XTH2-0300F-PT1 Cut Sheet



ProSense temperature transmitter, non-isolated, Pt100 RTD input, 0 to 300 deg F fixed, 4-20 mA output, 10 to 36 VDC operating voltage, DIN Form B connection head mount, screw terminals.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/XTH2-0300F-PT1>

## Technical Specifications

|                                             |                            |
|---------------------------------------------|----------------------------|
| <b>Brand</b>                                | ProSense                   |
| <b>Item</b>                                 | Temperature transmitter    |
| <b>Isolation</b>                            | Non-isolated               |
| <b>Field Configurable</b>                   | No                         |
| <b>Input RTD Signal Types</b>               | Pt100 RTD                  |
| <b>Factory Calibrated Temperature Range</b> | 0 to 300 deg F fixed       |
| <b>Output Current Signal Range</b>          | 4-20 mA                    |
| <b>Operating Voltage</b>                    | 10 to 36 VDC               |
| <b>Housing Material</b>                     | Polycarbonate              |
| <b>Mounting</b>                             | DIN Form B connection head |
| <b>Electrical Connection</b>                | Screw terminals            |
| <b>Includes</b>                             | Mounting hardware          |

## Agency Approvals

|                             |                                        |
|-----------------------------|----------------------------------------|
| <b>UL Listed File #</b>     | None                                   |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | 601711                                 |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |