

XTH2-ENC-F Cut Sheet



ProSense field housing, (2) 1/2in female NPT, -40 to +100 degrees C (-40 to 212 degrees F), aluminum, NEMA 4X, IP66 IP68. For use with programmable temperature transmitter XTH2-0-UNV-S and XTH2-0-UNV-P.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/XTH2-ENC-F>

Technical Specifications

Brand	ProSense
Item	Field housing
Electrical Connection	(2) 1/2in female NPT
Operating Temperature	-40 to +100 degrees C (-40 to 212 degrees F)
Material	Aluminum
NEMA Rating	4X
IP Rating	IP66 IP68
For Use With	Programmable temperature transmitter XTH2-0-UNV-S and XTH2-0-UNV-P
Additional Information	Order sensor and transmitter separately

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/XTH2-ENC-F.pdf>
See store item page for other formats.