

# XTH2-ENC-P Cut Sheet



ProSense connection head, 1/2in female NPT probe connection, 1/2in female NPT, -40 to +100 degrees C (-40 to 212 degrees F), aluminum, NEMA 4X, IP66 IP68. For use with programmable temperature transmitter XTH2-0-UNV-S and XTH2-0-UNV-P.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/XTH2-ENC-P>

## Technical Specifications

<b>Brand</b>	ProSense
<b>Item</b>	Connection head
<b>Probe Connection</b>	1/2in female NPT
<b>Electrical Connection</b>	1/2in female NPT
<b>Operating Temperature</b>	-40 to +100 degrees C (-40 to 212 degrees F)
<b>Material</b>	Aluminum
<b>NEMA Rating</b>	4X
<b>IP Rating</b>	IP66 IP68
<b>For Use With</b>	Programmable temperature transmitter XTH2-0-UNV-S and XTH2-0-UNV-P
<b>Additional Information</b>	Order sensor and transmitter separately

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/XTH2-ENC-P.pdf>  
See store item page for other formats.