

XTH2-N40140F-PT1 Cut Sheet



ProSense temperature transmitter, non-isolated, Pt100 RTD input, -40 to 140 deg F fixed, 4-20 mA output, 10-36 VDC operating voltage, DIN Form B connection head mount, screw terminals.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/XTH2-N40140F-PT1>

Technical Specifications

Brand	ProSense
Item	Temperature transmitter
Isolation	Non-isolated
Field Configurable	No
Input RTD Signal Types	Pt100 RTD
Factory Calibrated Temperature Range	-40 to 140 deg F fixed
Output Current Signal Range	4-20 mA
Operating Voltage	10-36 VDC
Housing Material	Polycarbonate
Mounting	DIN Form B connection head
Electrical Connection	Screw terminals
Includes	Mounting hardware

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	601711
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/XTH2-N40140F-PT1.pdf>
See store item page for other formats.