

XTP-360-0100C Cut Sheet



ProSense temperature sensor/transmitter, Pt100 RTD, compression probe, 0–100 °C, 360mm insertion length, 6mm probe diameter, Output: 1-channel, current, 4-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/XTP-360-0100C>

Technical Specifications

Brand	ProSense
Item	Temperature sensor/transmitter
Sensor Element	Pt100 RTD
Sensor Type	Compression probe
Media Type	Liquid, water, oil, chemicals, gases and air
Accuracy	Class A accuracy
Insertion Length	360mm
Probe Diameter	6mm
Sheath Material	316L stainless steel

Number Of Output Channels	1
Output	Current
Output Current Signal Range	4–20 mA
Operating Voltage	10–35 VDC
Electrical Connection	4-pin M12 quick-disconnect
Temperature Sensing Range	0–100 °C
IP Rating	IP66, IP67 and IP69
Additional Information	Purchase cable separately

Agency Approvals

UL Listed File #	None
UL Recognized File #	E311366
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/XTP-360-0100C.pdf>
See store item page for other formats.