

# XTP25N-100-0100C Cut Sheet



ProSense temperature transmitter, integral Pt100 RTD, 0 to 100 deg C, 6mm probe diameter, 100mm insertion length, 1/4in male NPT process connection, 4-20 mA analog output, 4-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/XTP25N-100-0100C>

## Technical Specifications

<b>Brand</b>	ProSense
<b>Item</b>	Temperature transmitter
<b>Sensor Type</b>	Integral Pt100 RTD
<b>Temperature Sensing Range</b>	0 to 100 deg C
<b>Probe Diameter</b>	6mm
<b>Insertion Length</b>	100mm
<b>Process Connection</b>	1/4in male NPT
<b>Analog Output</b>	4-20 mA
<b>Operating Voltage</b>	10-35 VDC
<b>Electrical Connection</b>	4-pin M12 quick-disconnect
<b>Additional Information</b>	Purchase cable separately

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E311366
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>