

# YA11-1-D-04-RN Cut Sheet



STAHL YA11 series audible alarm buzzer, hazardous location rated, 100 dB at 1m, 2.5 kHz to 3.1 kHz tone frequency, alternating fast two-tone tone(s), 24 VDC, panel mount, aluminium/ABS plastic housing, red, IP66, NEMA 4X.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/YA11-1-D-04-RN>

## Technical Specifications

Brand	STAHL
Item	Audible alarm buzzer
Series	YA11
Application	Hazardous location rated
Loudness Decibel	100 dB at 1m
Tone Frequency	2.5 kHz to 3.1 kHz
Tone Type	Alternating fast two-tone
Touch to Acknowledge	No
Voltage Rating	24 VDC
Mounting	Panel
Housing Material	Aluminium/ABS plastic
Color	Red
IP Rating	IP66
NEMA Rating	4X
Additional Information	Manufacturer part number: YA11/1-D-04-RN

## Agency Approvals

UL Listed File #	E161818
UL Recognized File #	None
UL Hazardous File #	E161818
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>