

YA11-1-D-11-RN Cut Sheet



STAHL YA11 series audible alarm buzzer, hazardous location rated, 100 dB at 1m, 1 kHz tone frequency, continuous tone(s), 24 VDC, panel mount, aluminium/ABS plastic housing, red, IP66, NEMA 4X.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/YA11-1-D-11-RN>

Technical Specifications

Brand	STAHL	Number of Alarms	1
Item	Audible alarm buzzer	Voltage Rating	24 VDC
Series	YA11	Mounting	Panel
Application	Hazardous location rated	Housing Material	Aluminium/ABS plastic
Loudness Decibel	100 dB at 1m	Color	Red
Tone Frequency	1 kHz	IP Rating	IP66
Tone Type	Continuous	NEMA Rating	4X
Touch to Acknowledge	No	Additional Information	Manufacturer part number: YA11/1-D-11-RN

Agency Approvals

UL Listed File #	E161818
UL Recognized File #	None
UL Hazardous File #	E161818
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/YA11-1-D-11-RN.pdf>
See store item page for other formats.