

YBB-14K4-0700-G012 Cut Sheet



Contrinex safety light curtain, sender/receiver pair, finger protection, 24 VDC, 14mm resolution, 653mm protected height, 0.25-3.5m operating distance, safety category Type 4, IP65 IP67, (2) 5-pin M12 quick-disconnects.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/YBB-14K4-0700-G012>

Technical Specifications

Brand	Contrinex
Item	Safety light curtain
Light Curtain Type	Sender/receiver pair
Function	Finger protection
Input Voltage	24 VDC
Beam Resolution	14mm
Protected Height	653mm
Operating Distance	0.25-3.5m
Safety Category	Type 4
Switching Output	(2) OSSD outputs
Connection	(2) 5-pin M12 quick-disconnects
IP Rating	IP65 IP67
Configurable	No
Includes	Mounting hardware and testing rod
Additional Information	Purchase cable separately

Agency Approvals

UL Listed File #	E321951
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document