

YBB-30R4-1600-G012 Cut Sheet



Contrinex safety light curtain, receiver, hand protection, 24 VDC, 30mm resolution, 1564mm protected height, 0.25-12m operating distance, safety category Type 4, IP65 IP67, 5-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/YBB-30R4-1600-G012>

Technical Specifications

| | | | |
|---------------------------|----------------------|-------------------------------|---|
| Brand | Contrinex | Safety Category | Type 4 |
| Item | Safety light curtain | Switching Output | (2) OSSD outputs |
| Light Curtain Type | Receiver | Connection | 5-pin M12 quick-disconnect |
| Function | Hand protection | IP Rating | IP65 IP67 |
| Input Voltage | 24 VDC | Configurable | No |
| Beam Resolution | 30mm | Includes | Mounting hardware and testing rod |
| Protected Height | 1564mm | Additional Information | Purchase sender YBB-30S4-1600-G012 to make a complete pair. Purchase cable separately |
| Operating Distance | 0.25-12m | | |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | e321951 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/YBB-30R4-1600-G012.pdf>
See store item page for other formats.