

YCA-50S4-3400-G012 Cut Sheet



Contrinex safety light curtain, sender, body protection, 24 VDC, 400mm resolution, 832mm protected height, 1-50m operating distance, safety category Type 4, IP65 IP67, 5-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/YCA-50S4-3400-G012>

Technical Specifications

Brand	Contrinex	Safety Category	Type 4
Item	Safety light curtain	Switching Output	(2) OSSD outputs
Light Curtain Type	Sender	Connection	5-pin M12 quick-disconnect
Function	Body protection	IP Rating	IP65 IP67
Input Voltage	24 VDC	Configurable	No
Beam Resolution	400mm	Includes	Mounting hardware and testing rod
Protected Height	832mm	Additional Information	Purchase receiver YCA-50R4-3400-G012 to make a complete pair. Purchase cable separately
Operating Distance	1-50m		

Agency Approvals

UL Listed File #	E321951
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/YCA-50S4-3400-G012.pdf>
See store item page for other formats.