


YN01-15505WL2000ST Cut Sheet



Sifam Tinsley B4 DC current shunt, 0–75 A, thru-bolt input connection, M4 screw output connection, 0–50 mV output, busbar mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/YN01-15505WL2000ST>

Technical Specifications

Brand	Sifam Tinsley
Series	B4
Item	DC current shunt
DC Current Range	0–75 A
Input Connection	Thru-bolt
Output Connection	M4 screw
Output Voltage Range	0–50 mV
Accuracy	±0.5%
Mounting	Busbar
Includes	Mounting hardware

Agency Approvals

UL Listed File #	None
UL Recognized File #	E471457
UL Hazardous File #	None
CE	View CE declarations
CSA File #	N/A
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/YN01-15505WL2000ST.pdf>
See store item page for other formats.