



Klemsan on-delay relay timer, 1–30 seconds selectable timing range, 24 VAC/VDC and 180–265 VAC operating voltage, 10A contact rating, (1) SPDT timed relay output(s), 35mm DIN rail mount, screw terminal(s).

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/Z1A-ND30S>

Technical Specifications

Brand	Klemsan
Item	Relay timer
Timer Type	On-delay
Indicator	LED
Timing Range	1–30 seconds selectable
Operating Voltage	24 VAC/VDC and 180–265 VAC
Timer Output Type(s)	(1) SPDT timed relay
Output Type	(1) N.O., (1) N.C.
Timer Function(s)	on-delay
Contact Rating	10A
Mounting	35mm DIN rail
Connector Type	Screw terminal(s)

Agency Approvals

UL Listed File #	E361956
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
[https://cdn.automationdirect.com
/static/drawings/2d/Z1A-ND30S.pdf](https://cdn.automationdirect.com/static/drawings/2d/Z1A-ND30S.pdf)
See store item page for other formats.